


Aluminum Van Ramp - Model AVR with Hook Nose



Note: Shown with **optional** Perforated Deck Surface. Perforations run down center 12 1/2" of ramp. Useable Width is 3" less than overall width.

1 1/4" Wide Hooks

Length

Low

We recommend using the ramp at no more than a 20 degree slope or 34% grade

Taper at Bottom End 5 1/2 degrees

<u>Overall Width</u>	<u>Centerline to Centerline dimension (A)</u>
29"	23 1/2"
35"	29 1/2"
39"	33 1/2"
41"	35 1/2"

Model No. AVR _____
With Hook Nose End

Capacity _____ lbs.

Weight _____ lbs.

Height Range _____ inches






Modern Light Metals, Inc.
920 Boyer Rd.
Coloma, MI 49038
Ph. 269-468-5041

Instructions for Hook Nose Van Ramp

Thank you for purchasing our Aluminum Van Ramp. MLM Van Ramps have been designed with the consumer in mind. You desire the highest possible ramp without compromising durability and longevity. We believe we have fulfilled consumer desires in this respect. Our serrated interlocking flooring gives excellent traction and is free of the bump at the entry end of the ramp commonly associated with many competitive brands of van ramps. Edges are smooth or rounded eliminating the possibility of tripping. Our quality construction should provide you with years of trouble free service.



Two slots are needed in the door sill for the ramp hooks. Reinforce with 1/8 x 1" bar.

<u>Overall Width</u>	<u>Centerline to Centerline dimension (A)</u>
29"	23 1/2"
35"	29 1/2"
39"	33 1/2"
41"	35 1/2"